

esco la2-4a1*ulpa,??>0.12??... ??????

ESCO Labculture Class II Type A2 & B2 biological safety & sterile workbench with exhaust air for the highest safety in the laboratory and cleanroom according to EN 12469. ... ESCO LA2 Labculture; Class II A2 & B2 biological safety & sterile workbench ... LA2-4A1-E: 1420 x 852 x 1540: 1270 x 623 x 670: 0.53/0.35 m/s: 2010671: LA2-5A1-E: 1725 x ...

Esco Labculture A2 (E) Esco 25 Esco Labculture ...

Summary of Contents for Esco Cytoculture LS2-4A1 Page 1 2940 Turnpike Drive, Units 15-16 o Hatboro, PA 19040, USA Toll-Free USA and Canada 1-877-479-3726 Tel 215-441-9661 o Fax 215-441-9660 us.escoglobal o usa@escoglobal Esco Micro Pte. Ltd. 21 Changi South Street 1 o Singapore 486 777 Tel +65 6542 0833 o Fax +65 6542 6920

- T? an to;n sinh h?c model LA2-4A1 v?i k?;ch th?c bu?ng l?;m vi?c 1.2m l?; d?;ng t? an to;n sinh h?c c?a Esco lo?i A2 b?o v? ng?i s? d?ng, b?o v? m?u v?t v?; b?o v? m?;i tr?ng theo ti?;u chu?n an to;n sinh h?c c?p ? 1, 2 v?; 3. - K?;ch th?c b?;n ngo?;i (WxDxH) = 1420x825x1540mm

Esco A2,??0755-27225204 18123982021 ???;shijing@szhrbio ??/ESCOEsco A2Esco Labculture A2 (E?) ??Esco25????? ... LA2-3A1;LA2-4A1;LA2-5A1;LA2-6A1;LA2-8A1:

Consult ESCO's entire Biological Safety Cabinets Labculture; LA2 catalogue on MedicalExpo. Page: 1/8. Exhibit with us ... Setback mode to further reduce power consumption by 60% Input Voltage motor voltage fluctuation airflow fluctuation Esco ECM motor stable motor voltage stable airflow ULPA Filter 10x Filtration efficiency of HEPA filter ...

Esco Labculture A2Esco25????? Esco Labculture ?????,????,?????????

Esco Labculture A2 (E?) ??Esco25????? Esco Labculture ?????,???

Esco Labculture; Class II Type A2 Biological Safety Cabinet (E-Series) blends the latest generation of energy-efficient DC ECM motor technology with Esco's experience of more than 25 years in biosafety cabinet

design. ... LA2-3A3-E: 230 VAC 60 Hz: LA2-4A1-E: 1420 x 852 x 1540 mm (56.0" x 33.5" x 60.6") 1270 x 623 x 670 mm (50.0" x 24.5" x 26.4 ...

Model No.	External Dimensions	Internal Dimensions	Airflow (Downflow)	Velocity	Airflow (Inflow)	Velocity
LA2-3A1-E	1115 x 852 x 1540 mm	(44.0" x 33.5" x 60.6")	970 x 623 x 670 mm	(38.2" x 24.5" x 26.4")	0.53 m/s	105 (fpm)
LA2-4A1-E	1420 x 852 x 1540 mm	(56.0" x 33.5" x 60.6")	970 x 623 x 670 mm	(38.2" x 24.5" x 26.4")	0.35 m/s	70 (fpm)

la2-4a1 Esco Labculture A2?????????Esco?????25????????????????????? Esco Labculture ?????????,?????,?? ...

Esco Labculture A2 (LA2) G4 series BSCs are full-sized, high performance, biological safety cabinets, designed to provide maximum operator and product protection, with large work zone ...

Esco's Laboratory Department has been designing and manufacturing Biological Safety Cabinets since the company was established in 1978. Over the subsequent 40 years, every opportunity has been taken to learn about product efficiency, design ergonomics and changing client requirements ... Figure 4: LA2-4A1-E. The Project . Esco was selected as ...

T? an toàn sinh h?c c?p II LA2-4A1-E ESCO ch? y?u s? d?ng ?? x? lý các m?u sinh h?c gây b?nh ho?c cho các ?ng d?ng yêu c?u khu v?c làm vi?c. MENU. Thi?t b? khoa h?c k? thu?t. T? ?m. T? ?m l?nh; T? ?m CO2;

T? an toàn sinh h?c c?p 2 Esco Labculture LA2-4A1-E lo?i A2 (E-Series) ?ng d?ng công ngh? ?ng c? ti?t ki?m n?ng l??ng DC ECM và s? d?ng 2 màng l?c ULPA v?i hi?u su?t l?c 99.999% t?? môi tr??ng an toàn, thu?n ti?n và phù h?p v?i nhi?u công vi?c ?òi h?i môi tr??ng không có s? xu?t hi?n c?a vi sinh v?t gây ...

Web: <https://triceratech.co.za>